
Question

[Anthony Filaski](#) · Nov 8, 2017

Maximum Size of HL7 Record

So this may sound trivial, but I'm seeing conflicting information on this topic and hoping to get clarification.

According to `Enslib.HL7.Message` class definition, the `maxlength` of `RawContent` is 10,000 characters. So when using encoding like UTF-8, that is 10KB. When using Unicode, that should then be 20KB.

But then also coming across some forums and documents where 32KB is maximum size before HL7 fields are truncated.

What is the sure way to determine and modify an interface's maximum supported message size?

[#Ensemble](#) [#DTL](#) [#HL7](#)

Source URL: <https://community.intersystems.com/post/maximum-size-hl7-record>